

Optical Sensing Interrogator | sm225



Applications

- Full Spectrum Measurements of fiber Bragg grating (FBG), extrinsic Fabry-Perot, long period grating (LPG), and other optical sensor components.
- Continuous lifetime health monitoring of bridges, dams, buildings, tunnels, ships, aircraft, trains, and other complex structures.
- Development of fiber optic sensors and transducers.

Features

- High accuracy absolute measurements of strain, temperature, pressure and other static sensors.
- On-board NIST traceable wavelength reference.
- Wide wavelength swept laser supporting more sensors per channel.
- Up to 16 integrated measurement channels.
- Direct mounting to any standard 19" EIA/ IEC equipment rack.

Deployments

- Civil structures (bridges, dams, tunnels, mines, buildings).
- Oil & gas (well reservoir management, platform structural health, pipeline condition)
- Marine vessels (hull, mast, rudder, deck, cargo containers).
- Transportation (railways, trains, roadways, specialty vehicles, cranes).
- Homeland security (perimeter intrusion, heat detection, security gate monitoring).

Description

The sm225 Optical Sensing Interrogator is an industrial grade, rack mounted static sensor interrogation module that facilitates up to 16 internal fiber measurement channels.

The sm225 Optical Sensing Interrogator is built upon the Micron Optics x25 optical interrogator core, featuring a high power, low noise swept wavelength laser, realized with Micron Optics patented Fiber Fabry-Perot Tunable Filter technology. The x25 interrogator core employs full spectral scanning and data acquisition, providing measurements with high absolute accuracy, flexible software post-processing, and high dynamic range performance. x25 based interrogators support continuous on-board NIST traceable wavelength reference components and are ideally suited to measure many different optical sensor types, including FBGs, long period gratings, extrinsic Fabry-Perot sensors, and many others. Well over half of the fiber optic sensors deployed today are measured with instrumentation that uses Micron Optics technology.

The Micron Optics "sm - Sensing Module" platform responds directly to the user commands of the optical interrogator core and outputs sensor wavelength data via Ethernet port and custom protocol. All module settings, sensor calculations, data visualization, storage, and alarming tasks are run on external pc or sensor processor module. The Sensing Module platform is ideal for custom, client developed system management tools, but is equally compatible with local or remote installations of Micron Optics ENLIGHT.



sm225 Rack Mount Module

Micron Optics ENLIGHT Sensing Analysis Software is included with Micron Optics sensing interrogator systems and provides a single suite of tools for data acquisition, computation, and analysis of optical sensor networks. ENLIGHT combines the useful features of traditional sensor software with the specific tools needed to optimize optical properties during the design, implementation, and operations phases of an optical sensor system. Tables, graphs, and additional data visualization features make ENLIGHT easy to use. Learn more about ENLIGHT at http://www.micronoptics.com/sensing_software.php.

Optical Sensing Interrogator | sm225

Specifications (R)

0 00 0 0 0000
000 00 0000
000000 00000
0 00 0 00 000
0 00 0 00 0
00 000 0 0000

sm225-800

pecifications (3)	SM225-200	SM225-500	sm225-800	
Optical Properties				
Number of Optical Channels	1	4	16	
Scan Frequency	1 Hz	2 Hz	0.5 Hz	
Wavelength Range	1520-1570 nm	1510-1590 nm	1510-1590 nm	
Wavelength Accuracy ²	10 pm	1 pm	1 pm	
Wavelength Stability ³	5 pm	1 pm	1 pm	
Wavelength Repeatability 4	0.5pm at 1Hz, 0.2 pm at 0.1Hz		1pm at 0.5Hz	
Dynamic Range ⁵	40dB	50 dB	40dB	
Full Spectrum Measurement	Included			
Internal Peak Detection Mode	Included			
Optical Connectors	FC/APC (E2000 available)			
Data Processing Capabilities				
Interfaces	Ethernet - other interfaces available via an optional Internal Sensing Processor			
Protocols	Custom Micron Optics protocol via Ethernet (others available)			
Remote Software	Spectral analysis, peak detection, data logger, peak tracking, and instrument control			
LabVIEW™ Source Code	Allows for customization of remote software			
Enhanced Data Management	ENLIGHT Sensing Analysis Software			
Mechanical, Environmental, El	ectrical Properties			
Dimensions; Weight	435 mm x 442 mm x 45 mm; 4.1 kg (9 lbs max)			
Rack Mount Hardware	Included			
Operating Temperature; Humidity	0° to 50°C; 0 to 80%, non-condensing			
Storage Temperature; Humidity	-20° to 70°C; 0 to 95%, non-condensing			

sm225-500

7 - 36 VDC (100~240 VAC, 47~63Hz), AC/DC converter included

20 W typ, 30 max

Options

Input Voltage

Power Consumption at 12V

Scan Frequency ⁶ 2, 5, or 10 Hz

Internal Sensing Processor w/ 3 Relays Windows XP Professional or Linux OS, See sp125 datasheet for processor specs

Notes:

- 1. Beta product. For details see www.micronoptics.com/product_designation.php.
- 2. Per NIST Technical Note 1297, 1994 Edition, Section D.1.1.1, definition of "accuracy of measurement".
- 3. Captures effects of long term use over full operating temperature range of the instrument.
- 4. Per NIST Technical Note 1297, 1994 Edition, Section D.1.1.2, definition of "repeatability [of results of measurements]".
- 5. Defined as laser launch power minus detection noise floor.
- 6. 10 Hz scan rate available with 40 nm (1525-1565nm) wavelength range.

